



Presets & Options:

- Vertical or horizontal drain
 - Sleeve ground-shortly or wall-shortly
 - Cold water, warm water, drain and electrical supply 230V or 400V must be presetted according to the regional directives
 - Microsection direction:
 - Cupboards: side-walls, back-walls and doors vertical;
 - Ground, cap, socket, shelves and light-bar horizontal;
 - Work-plate: horizontal in position of installation;
 - NAB: vertical front, horizontal socket
 - Faceplate: vertical front ; horizontal socket
- **ATTENTION:** Please, take note of the fire detector!

		Discher Technik GmbH Fuhr 4-6, 42781 Haan-Gruiten Tel.: +49 (0)2104/2336-0 Fax: +49 (0)2104/233699 E-mail: info@discher.de	Type of machine: Piccolo 500 DT	
Customer-No.:			Surface: Microsection - polished with 240 grain size - finished with 280 grain size	
Project-No.:	Status:			Material: 1.4301
Room:			Scale: 1:20	Measurements in mm
Date: 30.09.2014	Drawn by.: Schubert			Duplication or transfer to third parties, even in extracts, requires the written permission of the Discher Company GmbH. State of the art and subject to change without prior notice.
File name:				